

SOLVASY asking more from chemistry®

> SPECIALTY POLYMERS

solvene® EAP

Innovative Electro Active Polymers Designed to Bring New Features to Printed Electronics

Thanks to their intrinsic properties, solvene® EAP polymers do not need any specific or expensive post treatment process to be electro active. It can therefore be processed by various techniques, from classic extrusion to different printing techniques on various substrates, including flexible plastic films or paper.

solvene® EAP includes two polymer sub families:

Ferroelectric **solvene® P(VDF-TrFE) copolymers** exhibit a unique set of inherent piezo, pyro and ferroelectric properties:

- Piezo electricity: converting mechanical energy received through a mechanical stress into electrical energy, and conversely can deform under an electrical field (electro strictive properties)
- Pyro electricity: converting calorific energy into electrical energy, as temperature variations will change the dipole orientation and create a temporary electrical potential
- Ferroelectricity: as an organic ferroelectric material, solvene® EAP exhibits several advantageous properties including a large remnant polarization with excellent stability, a low leakage for high resistivity and switching times as short as 1 µs. Furthermore, it is intrinsically bistable, and does not require a voltage to keep its polarization state

Ferro-relaxor **solvene**[®] **T P(VDF-TrFE-CTFE) terpolymers** are easily solubilized in various solvents, showing unique properties such as:

- A very high dielectric constant above 20 which makes them perform quite well in gate dielectric in OFET or more generally in dielectric coating
- Good actuation power, giving high strain with low applied voltage
- Processability into thin films, allowing various actuators designs
- Large electrocaloric effect, paving the way for innovative heating and cooling systems

Polarization hysteresis – solvene® 250



solvene® EAP polymers are available in a variety of grades suitable for different applications, including ready-to-print formulations.

Key characteristics

	Unit	solvene® 200	solvene® 250	solvene® 300	solvene® T
Melting point	[°C]	145	146	145	128
Curie peak	[°C]	133	116	103	15
8	[25°C]	11	11	11	>20
d ₃₃ at 110Hz	[pC/N]	-25	-24	-22	n.a.

Transmittance and haze

	Air		Water	
	тт	Haze	тт	Haze
Sample	Average	Average	Average	Average
Not annealed	96.0	2.9	98.9	1.2
Annealed	95.3	4.8	97.4	2.2

Tested on 25-µm thick cast film using standard ASTM E313

www.solvay.com

SpecialtyPolymers.EMEA@solvay.com | Europe, Middle East and Africa SpecialtyPolymers.Americas@solvay.com | Americas SpecialtyPolymers.Asia@solvay.com | Asia Pacific



any of our products. Neither Solvay Specialty Polymers nor any of its affiliates makes any warranty, express or implied, including merchantability or fitness for use, or accepts any liability in connection with this product, related information or its use. Some applications of which Solvay's products may be proposed to be used are regulated or restricted by applicable laws and regulations or by national or international standards and in some cases by Solvay's recommendation, including applications of food/feed, water treatment, medical, pharmaceuticals, and personal care. Only products designated as part of the Solviva[®] family of biomaterials may be considered as candidates for use in implantable medical devices. The user alone must finally determine suitability of any information or products for any contemplated use in compliance with applicable law, the manner of use and whether any patents are infringed. The information and the products are for use by technically skilled persons at their own discretion and risk and does not relate to the use of this product in combination with any other substance or any other process. This is not a license under any patent or other proprietary right. All trademarks and registered trademarks are property of the companies that comprise Solvay Group or their respective owners.

Safety Data Sheets (SDS) are available by emailing us or contacting your sales representative. Always consult the appropriate SDS before using