




A Unique Approach to Composite Tooling

COMPOSITE MATERIALS



Solvay's innovation extends to providing a complete tooling solution to the customer part manufacturing experience, offering composite tooling materials and their process consumables, as well as a complete range of composite tooling design and hardware solutions. This unique combination of tool design, tool manufacture, and ongoing innovation in materials and process technologies makes Solvay a world leader in composite tooling.



Carbon fibre tool

Carbon fibre tool with Omega section aluminium inserts

A Real Competitive Advantage

Solvay's composite tooling expertise is second to none: through our expertise, technology, products, flexibility, technical support and wide-reaching network of partners, we offer innovation with real advantage to the composites industry, focusing on developing new material and tooling technologies to meet future demands.

The Most Extensive Offering

- Tooling prepreg suitable for use in all market sectors (unidirectional and fabric, using carbon and glass fibres).
- Compatible vacuum bagging consumables (low and high temperature capable).
- Full range of tooling ancillaries, including tooling block, backing structures and sealing systems.
- Tooling hardware manufacture, including composite tools, and reusable silicone tools.
- Worldwide manufacturing, design and technical support.
- Commitments to short lead-times from all sites.

Tooling Materials

With a broad product portfolio and customer focused distribution facilities, Solvay is truly a global one-stop shop for tooling and vacuum bagging materials.

Prepregs and Composite Materials

- Low temperature initial cure out-of-autoclave systems.
- Possibility to use of low cost/low temperature master models.
- Combination of good mechanical performance, toughness, leading to the manufacture of robust tooling.
- Bismaleimide prepregs for high temperature capable tooling.
- Ease of use with a broad processing window.
- · Excellent surface finish.

Composite Materials Product Selector Guide

	Product Form	Out Life (days)	Service Temp. °F (°C)	Cure Flexibility/Recommended Cure °F (°C)	Cure Method
DForm [®] Fabric	Epoxy Prepreg	3	356 (180)	8 hours at 140 (60) Post-cure 15 minutes at 392 (200) plus 8 hours at 374 (190)	Autoclave
CYFORM® 22	Epoxy Prepreg	3 to 4	350 (177)	168 hours at 68 (20) or 5 hours at 131 (55) Post-cure 5 hours at 390 (200)	Autoclave
CYFORM® 777	Epoxy Prepreg	12 to 15	350 (177)	48 hours at 122 (50) or 3 hours at 194 (90) Post-cure 5 hours at 390 (200)	Autoclave
CYFORM® 1-5-1	Epoxy Prepreg	3 to 4	356 (180)	40 hours at 95 (35) or 8 hours at 140 (60) Post-cure 15 minutes at 392 (200) plus 8 hours at 374 (190)	Autoclave
LTM [®] 12	Epoxy Prepreg	3	392 (200)	70 hours at 86 (30) or 5 hours at 158 (70) Post-cure 15 minutes at 392 (200) plus 8 hours at 374 (190)	Autoclave
LTM [®] 16	Epoxy Prepreg	6	392 (200)	70 hours at 104 (40) or 4 hours at 176 (80) Post-cure 15 minutes at 392 (200) plus 8 hours at 374 (190)	Autoclave
LTM [®] 202	Epoxy Prepreg	4	356 (180)	8 hours at 140 (60) Post-cure 15 minutes at 392 (200) plus 8 hours at 374 (190)	Autoclave
LTM® 205	Epoxy Prepreg for caul plates	21	356 (180)	Cure range: 176–248 (80–120) Post-cure 2 hours at 356 (180)	Vacuum/ Autoclave
LTM® 212	Epoxy Prepreg	2	392 (200)	40 hours at 95 (35) or 8 hours at 140 (60) Post-cure 15 minutes at 392 (200) plus 8 hours at 374 (190)	Autoclave
LTM [®] 217	Epoxy Prepreg	8	392 (200)	20 hours at 131 (55) or 5 hours at 176 (80) Post-cure 15 minutes at 392 (200) plus 8 hours at 374 (190)	Autoclave
DForm® Fabric	BMI Prepreg	45	374 (190)	6 hours at 350 (177) Post-cure 6 hours at 440 (226)	Autoclave
DURATOOL® 450	BMI prepreg	45	374 (190)	6 hours at 350 (177) Post-cure 6 hours at 440 (226)	Autoclave

Process Materials

Solvay offers a comprehensive range of vacuum bagging consumables, designed to work in perfect combination with tooling prepregs to optimise processing and produce the optimum tool surface and laminate quality - two essentials for tool usability and longevity.

These include:

- Vacuum bagging film
- Breather fabric
- Flow media
- Release film
- Peel ply
- Release fabric

- Sealant tape
- Adhesive tape
- Self-adhesive tool release
- Elastomers
- Tapes and sprays
- Combination products
- Prefabricated vacuum bags
- Reusable intensifiers and cauls
- Fittings and hoses for autoclave/oven
- Hoses, wrap and connectors for infusion

For long term component manufacturing, we offer two solutions to minimise part variability and ensure reproducible part quality:

- Reusable vacuum bag assemblies that can be added to the tool structures to create a complete tool solution.
- Fabricated pre-shaped vacuum bags which reduce labour time, materials waste and which enhance part to part consistency, if traditional vacuum bagging film solutions are preferred.


The manufacture of components from the composite tool can be further optimised through the integration of intensifiers and selectively reinforced cauls.

Process Materials Product Selector Guide

Prepreg product	Bagging film	Release film	Sealant tape	Peel ply	Breather	Flash tape	Hose	Valve
Epoxy tooling prepreg processing	HS8171 HS6262	A5000 A6000	SM5126 SM5142	D300 6001	RC3000-10 AB10HA	FT LETAPE	SILHOSER 93S	VBUF
BMI tooling prepreg processing	HB6262	A5000	SM5126	6001	AB40N (Nylon66) RC-3000-20	FT LETAPE	SILHOSER 93S	VBUF

Design

Solvay offers a confidential design and engineering service that benefits from 30 years' knowledge in tooling and significant experience in CATIA CAD, dimensional distortion software and FE analysis. This takes tooling projects from initial concept through all stages, including design, evaluation, prototyping and final manufacture.



Tooling Hardware

Solvay tooling knowledge and innovation capabilities is based upon many years of practical experience in tool building. This expertise has allowed us to continuously innovate and improve the knowledge and ability to service the broadest of customer challenges for tooling requirements. Our extensive tooling design and manufacturing capabilities are concentrated within our French facilities.

Silicone Tools

Our reusable vacuum systems, manufacturing techniques and sealing systems are amongst the most advanced in the industry.

Reusable membranes for high temperature autoclave applications, offering:

- Increased productivity and reduced operating costs and minimal product waste.
- Simplicity of use membranes can be applied to the most complex forms, allowing high volume production of good quality parts.
- Reliability robust membranes eliminate the risk of tearing during curing.

Heated membranes (flat mats and vacuuming membranes) for on-site repairs:

- Can be moulded to the shape of the work piece.
- Fitted with a frame or a ceiling skirt, they provide vacuum integrity without the need for consumables.

IMS (Infusion Membrane Silicone) membranes. Flexible, elastic and moulded to the precise form of the part, they incorporate the required resin feed networks, thus improving the infusion process. Benefits are:

- No need for films, i.e. savings in purchasing, cutting and recycling.
- Instant sealing so no resin leakage during infusion.
- Smooth interior surface to the infused part.
- Suitable for counter-tools.
- Easy to implement.
- Readily repaired and/or modified.



Reusable membrane

Carbon fibre tool with aluminium window frame

Intensifiers used for compaction problems on parts with complex angular or concave features, where resin accumulation is prevalent:

- Transmit vacuum bag pressure to localised, detailed areas on the part.
- Manufactured from silicone and fibrous carbon/ epoxy reinforcements, intensifiers provide a high level of rigidity and dimensional stability.
- Seal systems are fitted on the elastomeric tools for vacuum integrity. These accommodate complex shapes.

Composite Tools

With its large range of autoclave equipment, Solvay specialises in the manufacture of composites tools (glass/epoxy fibre, carbon epoxy fibre, BMI carbon fibre) for tight geometrical tolerances and large sizes. These moulds are created from relatively inexpensive masters, allowing duplication at a minimal cost. These tools can be mounted on adjustable frames or on carbon couplings.

Why Silicone Tools?

- Increase efficiency & reliability
- Savings labour hours
- Optimising material flow
- Improve process consistency
- Improve part quality
- Cost saving

Why Composite Tooling?

- Light
- Reusable
- Low CTE
- Good for complex geometries
- Can be processed at low temperature
- Combination of good mechanical performance, toughness, leading to the manufacture of robust tooling
- Provide excellent surface finish





Solvay

Composite Materials 4500 McGinnis Ferry Rd Alpharetta, GA 30005-3914 USA custinfo@solvay.com

Solvay

Composite Materials Composites House, Sinclair Close, Heanor Gate Industrial Estate, Heanor, Derbyshire, DE75 7SP, UK custinfo@solvay.com

www.solvay.com